


# CamContain™ GN Housing (gasket seal)



## Advantages

- Positive sealing integrity in a side access bag-in/bag-out housing for gasket seal Absolute® filters
- 1400 pounds of gasket-sealing pressure ensures complete capture of airborne contaminants. Designed for processes that use a decontamination procedure during filter change

**Typical applications:** Chemical manufacturing facilities, food processing, genetic research and biotechnology facilities, hospital isolation suites to prevent the spread of infectious diseases, industrial processes exhaust, microelectronic and semiconductor facilities, nuclear power plants, pharmaceutical facilities, radioisotope handling facilities, university research laboratories, US Department of Energy Facilities, veterinary research and animal disease laboratories, and specific United States Government and military facilities.

**Construction:** Containment level housing designed for filter decontamination at filter change. See Product Sheet 3405 for construction details.

**Filters:** Gasket seal Absolute® filters or HEPA filters. Designed for processes that use a decontamination procedure during filter change.

**Additional data:** Information shown herein for quick reference purposes only. Application specific data is required by the factory before model selection can be accomplished.

## Dimensions

Housing Size (H x W)	Pre-filter Depth (inches)	Primary Filter Depth (inches)	Height (inches)	Width (inches)	Weight (lbs)
Housing Size/Configuration Chart - 012-1GN					
½ x ½	N/A	12	15	26	125
½ x 1	N/A		27		165
1 x 1	N/A		27		198
1 x 2	N/A		51		305
1 x 3	N/A		75		410
2 x 1	N/A		27		350
2 x 2	N/A		51		540
2 x 3	N/A		75		720
3 x 1	N/A		27		500
3 x 2	N/A		51		770
3 x 3	N/A		75		1030
4 x 1	N/A		27		650
4 x 2	N/A		51		1000
4 x 3	N/A		75		1335
Housing Size/Configuration Chart - 016-1GN					

As part of our program for continuous improvement, Camfil reserves the right to change specifications without notice. 2018-10-12

**Housings (Containment)**

Housing Size (H x W)	Prefilter Depth (inches)	Primary Filter Depth (inches)	Height (inches)	Width (inches)	Weight (lbs)
½ x ½	N/A		15		135
½ x 1	N/A		27		180
1 x 1	N/A		27		215
1 x 2	N/A		51		330
1 x 3	N/A		75		445
2 x 1	N/A		27		380
2 x 2	N/A	16	51	30	580
2 x 3	N/A		75		780
3 x 1	N/A		27		545
3 x 2	N/A		51		830
3 x 3	N/A		75		1110
4 x 1	N/A		27		710
4 x 2	N/A		51		1080
4 x 3	N/A		75		1440

Housing Size/Configuration Chart - 018-1GN

½ x ½	N/A		15		145
½ x 1	N/A		27		195
1 x 1	N/A		27		230
1 x 2	N/A		51		350
1 x 3	N/A		75		470
2 x 1	N/A		27		400
2 x 2	N/A	18	51	33	615
2 x 3	N/A		75		820
3 x 1	N/A		27		615
3 x 2	N/A		51		575
3 x 3	N/A		75		1165
4 x 1	N/A		27		750
4 x 2	N/A		51		1140
4 x 3	N/A		75		1510

Housing Size/Configuration Chart - 212-1GN

½ x ½			15		125
½ x 1			27		165
1 x 1			27		195
1 x 2			51		305
1 x 3			75		410
2 x 1			27		350
2 x 2	2	12	51	26	540
2 x 3			75		720
3 x 1			27		500
3 x 2			51		770
3 x 3			75		1030
4 x 1			27		650
4 x 2			51		1000
4 x 3			75		1335

Housing Size/Configuration Chart - 216-1GN



## Housings (Containment)

Housing Size (H x W)	Prefilter Depth (inches)	Primary Filter Depth (inches)	Height (inches)	Width (inches)	Weight (lbs)
½ x ½			15		185
½ x 1			27		180
1 x 1			27		215
1 x 2			51		330
1 x 3			75		445
2 x 1			27		380
2 x 2	2	16	51	30	580
2 x 3			75		780
3 x 1			27		545
3 x 2			51		830
3 x 3			75		1110
4 x 1			27		710
4 x 2			51		1080
4 x 3			75		1440

Housing Size/Configuration Chart - 218-1GN

½ x ½			15		145
½ x 1			27		195
1 x 1			27		230
1 x 2			51		350
1 x 3			75		470
2 x 1			27		400
2 x 2	2	18	51	33	615
2 x 3			75		820
3 x 1			27		575
3 x 2			51		875
3 x 3			75		1165
4 x 1			27		750
4 x 2			51		1140
4 x 3			75		1510

Housing Size/Configuration Chart - 212-3GN

½ x ½			15		175
½ x 1			27		230
1 x 1			27		275
1 x 2			51		425
1 x 3			75		570
2 x 1			27		490
2 x 2	2,4,6	12	51	38	745
2 x 3			75		1000
3 x 1			27		705
3 x 2			51		1070
3 x 3			75		1430
4 x 1			27		920
4 x 2			51		1390
4 x 3			75		1860

Housing Size/Configuration Chart - 216-3GN

As part of our program for continuous improvement, Camfil reserves the right to change specifications without notice. 2018-10-12



**Housings (Containment)**

Housing Size (H x W)	Pre-filter Depth (inches)	Primary Filter Depth (inches)	Height (inches)	Width (inches)	Weight (lbs)
½ x ½			15		185
½ x 1			27		250
1 x 1			27		295
1 x 2			51		450
1 x 3			75		605
2 x 1			27		525
2 x 2	2,4,6	16	51	42	790
2 x 3			75		1060
3 x 1			27		750
3 x 2			51		1135
3 x 3			75		1510
4 x 1			27		980
4 x 2			51		1475
4 x 3			75		1965

Housing Size/Configuration Chart - 218-3GN

½ x ½			15		190
½ x 1			27		255
1 x 1			27		305
1 x 2			51		465
1 x 3			75		620
2 x 1			27		535
2 x 2	2,4,6	18	51	44	810
2 x 3			75		1085
3 x 1			27		770
3 x 2			51		1160
3 x 3			75		1545
4 x 1			27		1005
4 x 2			51		1510
4 x 3			75		2010

